



19" LED-Backlit Monitor Saves Energy and Reduces Eye Fatigue

LED Backlight

With an energy-saving LED backlight, the FlexScan S1903 uses only 11 watts during typical operation. The LED backlight does not contain any mercury for minimal environmental impact when the monitor is eventually disposed of.

Digital and Analog Inputs

With both DVI-D and D-Sub mini 15-pin inputs, you can use a computer that has either a digital or an analog graphics board (or both if connected to two computers), and quickly switch between the inputs via a front panel button.



Built-In Speakers

0.5-watt speakers are tucked away at the back of the monitor and out of view so you can enjoy sound while bezel size is kept to a minimum. A headphone jack is also built into the monitor.



Sync-On-Green Signal Support

Support for sync-on-green ensures this monitor can be used with legacy graphics boards that output this signal.

Compliance with International Labels




Auto Image Adjustment

The monitor discerns the input signal from the PC and automatically adjusts the clock, phase, image location, size, etc. In addition, the signal cables that are bundled were developed by EIZO to reduce noise.

Viewing Comfort with an Ergonomic Stand

Adjust the screen to the most comfortable position with 100 mm height adjustment, 30° tilt, 70° swivel, and 90° rotation for portrait mode. A basic stand that offers 35° of tilt is also available.




VESA Mount Version

For customers that will provide their own VESA-compatible mounting solutions, the FlexScan S1903 is available without a stand.


Optimized Brightness with Auto EcoView

The Auto EcoView function is a sensor on the front of the monitor that measures ambient light and optimizes the screen's brightness to a level akin to viewing a sheet of paper under typical office lighting conditions. Since the screen is never too bright, eye strain is reduced while power consumption is cut by up to 50% compared to operating the monitor with Auto EcoView turned off and set to the default factory brightness of 100%.




Anti-Glare Treatment

A non-glare screen reduces eye fatigue by dissipating reflective light that otherwise makes the screen difficult to view. Furthermore, the surface of the bezels is treated to prevent light reflection.



10-Bit Gamma Correction


This technology helps achieve accurate color by converting the 8-bit PC data to 10-bit, and assigning the ideal gamma values with a 10-bit look-up table (LUT) then returning the data to 8-bit format for display.




Improved Work Efficiency, Reduced Visual Fatigue

EIZO conducted a survey to establish the relationship between eye fatigue and monitor use. The survey found that when you properly adjust your monitor's brightness, the reduction in your ability to focus drops by half (Graph 1). In addition, maintaining correct working posture and taking regular breaks further reduced fatigue levels and increased work efficiency by 12.5% (Graph 2).

Comparison between fatigue levels after monitor use




Quantity of VDT work per unit of time



EIZO monitor features like Auto EcoView, ergonomic stands, and the EyeCare utility help reduce eye fatigue and increase work efficiency.

Preset Modes for Optimum Viewing

With EIZO's Fine Contrast function you can choose from several preset modes for the various applications you work with. Toggling between modes can be done manually in the OSD menu or automatically by assigning a mode to a particular application with the bundled ScreenManager Pro for LCD software.




Prevents Eye Fatigue in Dimly-Lit Offices

Fine Contrast includes an EyeCare mode that reduces the screen's brightness to just 3 cd/m². This ultra-low brightness helps prevent eye fatigue and increase productivity when working in an environment with very dim ambient lighting such as a CAD studio.


Closely Simulates Documents and Books

Paper mode simulates the look of printed paper by raising the black level and lowering the contrast ratio. Together with the Auto EcoView ambient brightness sensor, Paper mode reduces the amount of blue light emanating from the monitor for less eyestrain. (See page 4 for more information about Paper mode.)




Eye Care Utility

The EyeCare utility is EIZO-developed software that helps promote better work habits. It consists of a function called “EyeCare Reminder” that reminds you to take scheduled breaks.



Energy Savings across the Network

EIZO’s EcoView NET power management software provides centralized control over the power settings of monitors on a network. With EcoView NET, a systems administrator can confirm the settings for each monitor on the network, turn the power on or off, and if necessary, take measures to combat eye fatigue such as adjust the brightness or activate Auto EcoView. EcoView NET is available from EIZO distributors.



Made by EIZO


While outsourcing production is now common practice in the monitor industry, EIZO continues to manufacture its products the same way it has throughout its 40-year history – with its own staff at its own factories. This allows EIZO to maintain close control over production quality and offer the industry’s only 5-year manufacturer’s limited warranty.



Built to Last Five Years

EIZO’s five-year warranty is two years or 67% longer than the standard three-year warranty of most brands. Even if the initial purchase price of the FlexScan S1903 is higher than another 19-inch monitor, the TCO (total cost of ownership) will likely be lower due to the significantly longer buying cycle and less need for repair.

5-Year vs. 3-Year Warranty



Optional LCD Panel Protector

This protector fits easily between the LCD screen and bezel, has a light transmission rate of more than 90%, and includes both an anti-glare coating side to reduce light reflection and a glossy side for crisper, more vibrant images.



What is Paper Mode?

Simply put, it is a mode which adjusts the brightness, contrast ratio, and color temperature of a monitor to simulate those of printed paper. Over the course of a work day PC users must constantly adjust to the difference between how monitors and paper appear. This overworks the muscles of the eyes and is thought to be a source of eye fatigue and stress. Paper mode was developed to alleviate the eye fatigue and stress that PC users feel.

Comparison between paper, EIZO square monitors, and Paper Mode

	Newspaper	Recycled Copy Paper	EIZO Square Monitors	Paper Mode
Brightness	55 % reflection rate, 88 cd/m ² *	70 % reflection rate, 112 cd/m ² *	267 cd/m ² †	50 - 70 % reflection rate
Contrast Ratio	6.2:1	10.7:1	1167:1†	About 30:1
Color Temperature	3,477 K	3,828 K	6500 K (when shipped)	4,000 - 5,000 K

* Measured at an ambient brightness of 500 lx. † Average maximum brightness of FlexScan square monitors.


Color Temperature, Brightness and the Effect on Blue Light

In the visible light spectrum, blue light has wavelengths adjacent to ultraviolet light. Compared to the factory preset setting of 6,500 K of typical LCD monitors, Paper Mode is closer to the spectral distribution with long reddish wavelengths so it reduces the amount of blue light, a cause of eye fatigue.



The combination of Paper Mode and the Auto EcoView brightness adjustment function reduces blue light even more. In a monitor with an LED backlight where Paper Mode and Auto EcoView were used, the blue light was measured and found to have only 1/6th the intensity of the factory setting.

Effect of Lowering Brightness and Color Temperature



SPECIFICATIONS

Cabinet Colors	Gray, Black
Panel Type	TN
Backlight	LED
Size	19" / 48 cm (481 mm diagonal)
Native Resolution	1280 x 1024 (5:4 aspect ratio)
Display Size (H x V)	376.3 x 301.0 mm
Pixel Pitch	0.294 x 0.294 mm
Display Colors	16.77 million from a palette of 1.06 billion
Viewing Angles (H / V, typical)	170°, 160°
Brightness (typical)	250 cd/m ²
Contrast Ratio (typical)	1000:1
Response Time (typical)	5 ms (black-white-black)
Video Signals	D-Sub mini 15 pin, DVI-D 24 pin (with HDCP)
Digital Scanning Frequency (H / V)	31 - 64 kHz, 59 - 61 Hz (VGA Text: 69 - 71 Hz)
Analog Scanning Frequency (H / V)	31 - 80 kHz, 50 - 75 Hz
Sync Formats	Separate, Sync on green
Speakers	0.5 W + 0.5 W
Input Terminals	3.5 mm stereo jack
Output Terminals	3.5 mm headphone jack
Sound Adjustment	Volume
Power Requirements	AC 100 - 120 V / 200 - 240 V, 50 / 60 Hz
Maximum Power Consumption	23 W
Typical Power Consumption	11 W
Power Save Mode	Less than 0.5 W
Power Management	Power Save (VESA DPM and DVI DMPM), Eco Timer
Pre-set Modes	FineContrast (Text, sRGB, EyeCare, Paper, Custom)
Auto EcoView	Yes
OSD Languages	English, French, German, Italian, Japanese, Simplified and Traditional Chinese, Spanish, Swedish
Others	Screen Adjustment (Clock, Phase, Position, Range (Auto), Smoothing (5 stages), Color Adjustment (Brightness, Contrast, Temperature, Gain, Reset), Input Signal, Power Indicator, Product Information (name, serial number, resolution, operating time, etc.), OSD Menu Position, Adjustment Lock, DDC/CI Lock, Reset
Dimensions (Landscape, W x H x D)	With Height Adjustable Stand: 405 x 406.5 - 506.5 x 205 mm With Tilt Stand: 405 x 416 x 205 mm
Dimensions (Without Stand, W x H x D)	405 x 334 x 61.5 mm
Net Weight	With Height Adjustable Stand: 5.9 kg With Tilt Stand: 4.9 kg
Net Weight (Without Stand)	4.1 kg
Height Adjustment Range	With Height Adjustable Stand: 100 mm With Tilt Stand: -
Tilt	With Height Adjustable Stand: 30° Up, 0° Down With Tilt Stand: 30° Up, 5° Down
Swivel	With Height Adjustable Stand: 35° Right / 35° Left With Tilt Stand: -
Pivot	With Height Adjustable Stand: 90° With Tilt Stand: -
Hole Spacing (VESA Standard)	100 x 100 mm
Temperature	5 - 35 °C
Humidity (R.H., non condensing)	20 - 80 %
Certifications & Standards	TCO Displays 6.0, EPEAT Gold (except for Tilt Stand version) / Silver (Tilt Stand version) (US), TUV/Ergonomics (including ISO9241-307), TUV/GS, C-Tick, CE, CB, cTUVus, FCC-B, Canadian ICES-003-B, TUV/S, VCCI-B, EPA Energy Star, RoHS, WEEE, China RoHS, CCC, GOST-R
Supplied Accessories	AC power cord, signal cables (D-Sub - D-Sub, DVI-D - DVI-D), audio cable, setup guide, CD-ROM (PDF user's manual, ScreenManager Pro for LCD [DDC/CI], ScreenSlicer software)
Warranty	Five Years

¹ The usage time is limited to 30,000 hours or less, and the warranty period of the LCD panel is limited to three years from the date of purchase.

EIZO Corporation

153 Shimokashiwano, Hakusan, Ishikawa 924-8566 Japan

Phone +81-76-277-6792 Fax +81-76-277-6793

www.eizo.com

All product names are trademarks or registered trademarks of their respective companies. EIZO and FlexScan are registered trademarks of EIZO Corporation. Specifications are subject to change without notice.

Copyright©2013 EIZO Corporation. All rights reserved.